


O-ring
Anelli di rinforzo/Serie P

Diagram showing O-ring cross-sections and dimensions. Includes a table with columns: Tipo, Materiale, Durezza (JIS H), Colore, Gamma temp. operativa, Simbolo JIS, Applicazioni, and Caratteristiche. Rows include NPA, NPB, NPSW, NPS, NPF, NPFH, NPEG, and NPBR. Below the table are diagrams for dimensions W, D, d, and G, and a note about NPS color.

Misura raccordo dettagliata

Table with 7 columns: Tipo, N., Dimensione G (Tolleranza +0.25/-0), Dimensione H ±0.05, Valore max dimensione R. Rows include NPA, NPB, NPSW, NPS, NPF, NPFH, NPEG, and NPBR with various size ranges like 3~10, 10A~22, 22A~50, and 50A~80.

- ① Quando viene applicata una pressione interna a un O-ring per montaggio su superficie, progettare la struttura in modo che la circonferenza esterna dell'O-ring sia a stretto contatto con la parete esterna della gola.
- ② Quando si utilizza un O-ring per montaggio su superficie per una pressione interna, se la lunghezza di D è 30 mm o inferiore, maggiorare la lunghezza di 0.2 - 0.3 mm.
- ③ Le dimensioni della gola sono di riferimento.



Anelli di rinforzo JIS B 2407 (Per serie P, taglio ad angolo)

Table with 11 columns: Cod. comp., Tipo, N. nominale O-ring applicabili, W, d, D, T, Prezzo unitario, and Sconto volumi elevati. It lists various reinforced O-ring types (NPBR) with their dimensions and pricing.

Serie P JIS B 2401 (Per montaggio, dinamici)

Large table with 24 columns: Cod. comp., Tipo, N., Numero nominale JIS, W, do, Tolleranza NPA, NPB, D.I., Tolleranza NPS, NPSW, NPEG, Tolleranza NPF, NPFH, Materiale corrispondente, and 12 columns for pricing (Prezzo unitario, Sconto volumi elevati) for various series (NPF, NPB, NPSW, NPS, NPF, NPFH, NPEG).