

Alberi rotanti Tolleranza D h9 (Trafilati a freddo)/h7 (Rettificati)/g6 (Rettificati)
Dritti

Scegliere tra h9 (Trafilati a freddo), h7 (Rettificati) e g6 (Rettificati) a seconda dell'applicazione.

Diagram showing shaft types and specifications. Includes a table for Tipo, Tolleranza D, Materiale, and Trattamento superficie. Also includes a table for Circolarità e rettilineità and a table for Tolleranza dimensione L.

h9 (Trafilati a freddo)

Table with 4 columns: Tipo, Codice componente, D h9, and L=Incrementi di 0.1mm. Rows include SFMR, PSFMR, and SSFMR with various tolerance values.

h7 (Rettificati)

Table with 4 columns: Tipo, Codice componente, D h7, and L=Incrementi di 0.1mm. Rows include SFHR, PSFHR, and SSFHR with various tolerance values.

g6 (Rettificati)

Table with 4 columns: Tipo, Codice componente, D g6, and L=Incrementi di 0.1mm. Rows include SFR, PSFR, SSFR, HFR, and PHFR with various tolerance values.

Ordering Example: Codice componente - L. SFMR15 - 150, PSFHR20 - 300.

h9 (Trafilati a freddo)

Table with 18 columns: Tipo, D, and various tolerance values for SFMR, PSFMR, and SSFMR.

h7 (Rettificati) g6 (Rettificati)

Table with 18 columns: Tipo, D, and various tolerance values for SFHR, PSFHR, SSFHR, SFR, PSFR, and SSFR.

Table with 18 columns: Tipo, D, and various tolerance values for HFR and PHFR.

Alterations section showing examples of SFMR30 and KC20-A10 with dimensions L and D.

Technical specifications section. Includes diagrams and tables for Variants (Sede chiavetta, Sede vite di fermo, 2 sedi vite fermo, Gola per camma, Sedi chiave), Codice (KC, WKC, FC, WFC, KFC, UC, SC, LKC), and Spec. (Detailed dimensions and tolerances for each variant).