


Molle con filo a sezione rotonda

Riferimento D.E. in acciaio inox



UM: Fmax (Deflessione ammessa) = LxFa%

Codice componente	D-L	d	Lun- ghezza a blocco	F max	N{kgf} max	Fa%	Prezzo unitario
UM 4-	5*	0.4	2.2	1.75	3.4 (0.35)	35	
	10*	0.5	4.9	3.5	6.8 (0.7)		
	15	0.55	7.5	5.25	10.3 (1.05)		
	20	0.6	11.1	7	13.7 (1.4)		
	25	0.6	11.1	8.75	17.2 (1.75)		
30	0.65	16.3	10.5	20.6 (2.1)			
UM 5-	5*	0.45	2.25	1.75	3.4 (0.35)	35	
	10*	0.5	3.13	3.5	6.8 (0.7)		
	15	0.65	8.45	5.25	10.3 (1.05)		
	20	0.65	8.45	7	13.7 (1.4)		
	25	0.7	11.9	8.75	17.2 (1.75)		
30	0.7	11.9	10.5	20.6 (2.1)			
35	0.75	16.5	12.25	24.0 (2.45)			
40	0.8	23.2	14	27.5 (2.8)			
45	0.8	23.2	15.75	30.9 (3.15)			
50	0.85	31.45	17.5	34.3 (3.5)			
UM 6-	5*	0.55	2.7	1.7	4.9 (0.5)	35	
	10	0.7	5.6	3.5	10.8 (1.1)		
	15	0.75	7.4	5.2	15.7 (1.6)		
	20	0.75	7.4	7	20.6 (2.1)		
	25	0.85	12.8	8.7	25.5 (2.6)		
30	0.85	12.8	10.5	31.4 (3.2)			
35	0.9	16.7	12.2	36.3 (3.7)			
40	0.9	16.8	14	41.2 (4.2)			
45	1.0	27.8	15.8	46.1 (4.7)			
50	1.0	28.0	17.5	52.0 (5.3)			
60	1.0	28.0	18	53.0 (5.4)	30		
70	1.1	46.2	20	58.8 (6)	28		
UM 8-	10	0.85	6.4	3.5	10.8 (1.1)	35	
	15	0.9	7.9	5.2	15.7 (1.6)		
	20	0.9	7.9	7	20.6 (2.1)		
	25	0.9	7.9	8.7	25.5 (2.6)		
	30	1.0	12.0	10.5	31.4 (3.2)		
35	1.0	12.0	12.2	36.3 (3.7)			
40	1.1	18.7	14	41.2 (4.2)			
45	1.1	18.7	15.8	46.1 (4.7)			
50	1.1	18.7	17.5	52.0 (5.3)			
60	1.2	28.2	21	61.8 (6.3)			
70	1.3	42.0	24.5	72.6 (7.4)			

- * Per i tipi con *, le due estremità non sono rettificare.
- † I valori della lunghezza a blocco sono solo di riferimento. Possono esserci alcune variazioni in base al lotto.
- ‡ Numero utilizzi: 1 milione di volte



Varianti	Codice	Spec.																																																										
		Modifica lunghezza e tolleranza della costante molla (vedere la tabella riportata sotto).																																																										
		<table border="1"> <thead> <tr> <th>Codice componente</th> <th>L</th> <th>Varianti</th> <th>Tolleranza</th> <th>Tolleranza costante molla</th> </tr> </thead> <tbody> <tr> <td rowspan="10">UM</td> <td>4</td> <td>15, 20</td> <td></td> <td>±0.4</td> </tr> <tr> <td></td> <td>25, 30</td> <td></td> <td>±0.5</td> </tr> <tr> <td></td> <td>15, 20</td> <td></td> <td>±0.4</td> </tr> <tr> <td></td> <td>25-50</td> <td></td> <td>±0.5</td> </tr> <tr> <td></td> <td>10-20</td> <td></td> <td>±0.4</td> </tr> <tr> <td></td> <td>25-50</td> <td></td> <td>±0.5</td> </tr> <tr> <td></td> <td>60, 70</td> <td></td> <td>±0.8</td> </tr> <tr> <td></td> <td>15-30</td> <td></td> <td>±0.5</td> </tr> <tr> <td></td> <td>35-50</td> <td></td> <td>±0.5</td> </tr> <tr> <td></td> <td>60, 70, 80</td> <td></td> <td>±0.8</td> </tr> <tr> <td></td> <td>20-30</td> <td></td> <td>±0.5</td> </tr> <tr> <td></td> <td>35-50</td> <td></td> <td>±0.5</td> </tr> <tr> <td></td> <td>60, 70, 80</td> <td></td> <td>±0.8</td> </tr> </tbody> </table>	Codice componente	L	Varianti	Tolleranza	Tolleranza costante molla	UM	4	15, 20		±0.4		25, 30		±0.5		15, 20		±0.4		25-50		±0.5		10-20		±0.4		25-50		±0.5		60, 70		±0.8		15-30		±0.5		35-50		±0.5		60, 70, 80		±0.8		20-30		±0.5		35-50		±0.5		60, 70, 80		±0.8
Codice componente	L	Varianti	Tolleranza	Tolleranza costante molla																																																								
UM	4	15, 20		±0.4																																																								
		25, 30		±0.5																																																								
		15, 20		±0.4																																																								
		25-50		±0.5																																																								
		10-20		±0.4																																																								
		25-50		±0.5																																																								
		60, 70		±0.8																																																								
		15-30		±0.5																																																								
		35-50		±0.5																																																								
		60, 70, 80		±0.8																																																								
	20-30		±0.5																																																									
	35-50		±0.5																																																									
	60, 70, 80		±0.8																																																									
		‡ Le due estremità sono rettificare. † Per ordini superiori ai valori indicati, controllare con WOS.																																																										

UH: Fmax (Deflessione ammessa) = LxFa%

Codice componente	D-L	d	Lun- ghezza a blocco	F max	N{kgf} max	Fa%	Prezzo unitario
UH 4-	5*	0.45	2.7	1.5	4.4 (0.45)	30	
	10*	0.5	3.8	3	8.8 (0.9)		
	15	0.6	8.1	4.5	13.2 (1.35)		
	20	0.65	11.7	6	17.6 (1.8)		
	25	0.7	16.8	7.5	22.1 (2.25)		
30	0.7	16.8	9	26.5 (2.7)			
UH 5-	5*	0.55	3.3	1.5	4.4 (0.45)	30	
	10	0.6	4.65	3	8.8 (0.9)		
	15	0.6	4.65	4.5	13.2 (1.35)		
	20	0.75	11.81	6	17.6 (1.8)		
	25	0.75	11.81	7.5	22.1 (2.25)		
30	0.8	16	9	26.5 (2.7)			
35	0.85	21.68	10.5	30.9 (3.15)			
40	0.85	21.68	12	35.3 (3.6)			
45	0.9	28.8	13.5	39.7 (4.05)			
UH 6-	5*	0.65	3.2	1.5	8.8 (0.9)	30	
	10	0.7	3.9	3	17.7 (1.8)		
	15	0.85	7.7	4.5	26.5 (2.7)		
	20	0.9	9.7	6	35.3 (3.6)		
	25	1.0	15.5	7.5	44.1 (4.5)		
30	1.0	15.5	9	53.0 (5.4)			
35	1.1	24.8	9.8	57.9 (5.9)	28		
40	1.1	24.8	10	58.8 (6)	25		
45	1.1	24.8	11.3	66.7 (6.8)			
50	1.2	39.0	10	58.8 (6)	20		
60	1.2	39.0	14	82.4 (8.4)	23		
70	1.2	39.0	15	88.3 (9)	21		
UH 8-	10	0.9	5.3	3	17.7 (1.8)	30	
	15	0.9	5.3	4.5	26.5 (2.7)		
	20	1.1	11	6	35.3 (3.6)		
	25	1.1	11	7.5	44.1 (4.5)		
	30	1.2	15.9	9	53.0 (5.4)		
35	1.2	15.9	10.5	61.8 (6.3)			
40	1.3	23.1	12	70.6 (7.2)			
45	1.3	23.1	13.5	79.4 (8.1)			
50	1.4	33.3	15	88.3 (9)			
60	1.4	33.3	18	105.9 (10.8)			
70	1.5	48.0	19	111.8 (11.4)	27		



Costante molla

Tipologia	UV	UY	UR	UF	UL	UTT	UM	UH	UBB
2		0.05(0.005)	0.2(0.02)	0.3(0.03)	0.5(0.05)				
3									
4	N/mm 0.05 (kgf/mm) {0.005}	N/mm 0.098 (kgf/mm) {0.01}				N/mm 1.5 (kgf/mm) {0.15}	2.0{0.2}	2.9{0.3}	4.9{0.5}
5									
6			N/mm 0.29 (kgf/mm) {0.03}	N/mm 0.49 (kgf/mm) {0.05}	N/mm 0.98 (kgf/mm) {0.1}				
8						N/mm 2.0 (kgf/mm) {0.2}			
10							N/mm 2.9 (kgf/mm) {0.3}	N/mm 5.9 (kgf/mm) {0.6}	N/mm 9.8 (kgf/mm) {1.0}
12		N/mm 0.2 (kgf/mm) {0.02}							
13									
14									
16									
20		0.3(0.03)	0.5(0.05)	0.98(0.1)	2.9(0.3)	3.9(0.4)	4.9(0.5)	14.7(1.5)	29.4(3.0)
Fmax	F=Lx70%	F=LxFa%	F=LxFa%	F=Lx45%	F=Lx40%	F=LxFa%	F=LxFa%	F=LxFa%	F=LxFa%



Varianti	Codice	Spec.																																																										
		Modifica lunghezza e tolleranza della costante molla (vedere la tabella riportata sotto).																																																										
		<table border="1"> <thead> <tr> <th>Codice componente</th> <th>L</th> <th>Varianti</th> <th>Tolleranza</th> <th>Tolleranza costante molla</th> </tr> </thead> <tbody> <tr> <td rowspan="10">UH</td> <td>4</td> <td>15, 20</td> <td></td> <td>±0.4</td> </tr> <tr> <td></td> <td>25, 30</td> <td></td> <td>±0.5</td> </tr> <tr> <td></td> <td>10-20</td> <td></td> <td>±0.4</td> </tr> <tr> <td></td> <td>25-45</td> <td></td> <td>±0.5</td> </tr> <tr> <td></td> <td>10-20</td> <td></td> <td>±0.4</td> </tr> <tr> <td></td> <td>25-50</td> <td></td> <td>±0.5</td> </tr> <tr> <td></td> <td>60, 70</td> <td></td> <td>±0.8</td> </tr> <tr> <td></td> <td>15-30</td> <td></td> <td>±0.5</td> </tr> <tr> <td></td> <td>35-50</td> <td></td> <td>±0.5</td> </tr> <tr> <td></td> <td>60, 70, 80</td> <td></td> <td>±0.8</td> </tr> <tr> <td></td> <td>20-30</td> <td></td> <td>±0.5</td> </tr> <tr> <td></td> <td>35-50</td> <td></td> <td>±0.5</td> </tr> <tr> <td></td> <td>60, 70, 80</td> <td></td> <td>±0.8</td> </tr> </tbody> </table>	Codice componente	L	Varianti	Tolleranza	Tolleranza costante molla	UH	4	15, 20		±0.4		25, 30		±0.5		10-20		±0.4		25-45		±0.5		10-20		±0.4		25-50		±0.5		60, 70		±0.8		15-30		±0.5		35-50		±0.5		60, 70, 80		±0.8		20-30		±0.5		35-50		±0.5		60, 70, 80		±0.8
Codice componente	L	Varianti	Tolleranza	Tolleranza costante molla																																																								
UH	4	15, 20		±0.4																																																								
		25, 30		±0.5																																																								
		10-20		±0.4																																																								
		25-45		±0.5																																																								
		10-20		±0.4																																																								
		25-50		±0.5																																																								
		60, 70		±0.8																																																								
		15-30		±0.5																																																								
		35-50		±0.5																																																								
		60, 70, 80		±0.8																																																								
	20-30		±0.5																																																									
	35-50		±0.5																																																									
	60, 70, 80		±0.8																																																									
		‡ Le due estremità sono rettificare. † Per ordini superiori ai valori indicati, controllare con WOS.																																																										