


Molle a spirale

Carico leggero SWL



D	d	L	Costante molla N/mm(kgf/mm)	F=Lx32%		F=Lx36%		F=Lx40%		Codice componente	Prezzo unita- rio
				Fmm	Carico N(kgf)	Fmm	Carico N(kgf)	Fmm	Carico N(kgf)	D-L	
6	3	15	13.1(1.33)	4.8	63 {6.4}	5.4	71 {7.2}	6.0	78 {8.0}	SWL 6-	15
		20	9.8(1.00)	6.4		7.2		8.0		20	
		25	7.8(0.80)	8.0		9.0		10.0		25	
		30	6.5(0.67)	9.6		10.8		12.0		30	
		35	5.6(0.57)	11.2		12.6		14.0		35	
		40	4.9(0.50)	12.8		14.4		16.0		40	
8	4	10	24.5(2.50)	3.2	78 {8.0}	3.6	88 {9.0}	4.0	98 {10}	SWL 8-	10
		15	16.3(1.67)	4.8		5.4		6.0		15	
		20	12.3(1.25)	6.4		7.2		8.0		20	
		25	9.8(1.00)	8.0		9.0		10.0		25	
		30	8.2(0.83)	9.6		10.8		12.0		30	
		35	7.0(0.71)	11.2		12.6		14.0		35	
		40	6.1(0.63)	12.8		14.4		16.0		40	
		45	5.4(0.56)	14.4		16.2		18.0		45	
		50	4.9(0.50)	16.0		18.0		20.0		50	
		55	4.5(0.45)	17.6		19.8		22.0		55	
		60	4.1(0.42)	19.2		21.6		24.0		60	
		65	3.8(0.38)	20.8		23.4		26.0		65	
		70	3.5(0.36)	22.4		25.2		28.0		70	
		75	3.3(0.33)	24.0		27.0		30.0		75	
80	3.1(0.31)	25.6	28.8	32.0	80						
10	5	10	34.3(3.50)	3.2	110 {11}	3.6	124 {13}	4.0	137 {14}	SWL 10-	10
		15	22.9(2.33)	4.8		5.4		6.0		15	
		20	17.2(1.75)	6.4		7.2		8.0		20	
		25	13.7(1.40)	8.0		9.0		10.0		25	
		30	11.4(1.17)	9.6		10.8		12.0		30	
		35	9.8(1.00)	11.2		12.6		14.0		35	
		40	8.6(0.88)	12.8		14.4		16.0		40	
		45	7.6(0.78)	14.4		16.2		18.0		45	
		50	6.9(0.70)	16.0		18.0		20.0		50	
		55	6.2(0.64)	17.6		19.8		22.0		55	
		60	5.7(0.58)	19.2		21.6		24.0		60	
		65	5.3(0.54)	20.8		23.4		26.0		65	
		70	4.9(0.50)	22.4		25.2		28.0		70	
		75	4.6(0.47)	24.0		27.0		30.0		75	
80	4.3(0.44)	25.6	28.8	32.0	80						
90	3.8(0.39)	28.8	32.4	36.0	90						
12	6	15	34.3(3.50)	4.8	165 {17}	5.4	185 {19}	6.0	206 {21}	SWL 12-	15
		20	25.7(2.63)	6.4		7.2		8.0		20	
		25	20.6(2.10)	8.0		9.0		10.0		25	
		30	17.2(1.75)	9.6		10.8		12.0		30	
		35	14.7(1.50)	11.2		12.6		14.0		35	
		40	12.9(1.31)	12.8		14.4		16.0		40	
		45	11.4(1.17)	14.4		16.2		18.0		45	
		50	10.3(1.05)	16.0		18.0		20.0		50	
		55	9.4(0.95)	17.6		19.8		22.0		55	
		60	8.6(0.88)	19.2		21.6		24.0		60	
		65	7.9(0.81)	20.8		23.4		26.0		65	
		70	7.4(0.75)	22.4		25.2		28.0		70	
		75	6.9(0.70)	24.0		27.0		30.0		75	
		80	6.4(0.66)	25.6		28.8		32.0		80	
90	5.7(0.58)	28.8	32.4	36.0	90						
14	7	20	34.3(3.50)	6.4	220 {22}	7.2	247 {25}	8.0	275 {28}	SWL 14-	20
		25	27.5(2.80)	8.0		9.0		10.0		25	
		30	22.9(2.33)	9.6		10.8		12.0		30	
		35	19.6(2.00)	11.2		12.6		14.0		35	
		40	17.2(1.75)	12.8		14.4		16.0		40	
		45	15.3(1.56)	14.4		16.2		18.0		45	
		50	13.7(1.40)	16.0		18.0		20.0		50	
		55	12.5(1.27)	17.6		19.8		22.0		55	
		60	11.4(1.17)	19.2		21.6		24.0		60	
		65	10.6(1.08)	20.8		23.4		26.0		65	
		70	9.8(1.00)	22.4		25.2		28.0		70	
		75	9.2(0.93)	24.0		27.0		30.0		75	
		80	8.6(0.88)	25.6		28.8		32.0		80	
		90	7.6(0.78)	28.8		32.4		36.0		90	
100	6.9(0.70)	32.0	36.0	40.0	100						
Numero utilizzi			1 milione di volte		500,000 volte		300,000 volte				